



181112



Push-button, NO contact, TS, gold glossy, 24-carat galvanised

Technical Features

Electric current

|                           |        |
|---------------------------|--------|
| Momentary contact current | 1.50 A |
|---------------------------|--------|

Voltage

|               |      |
|---------------|------|
| Rated voltage | 12 V |
|---------------|------|

Architecture

|                           |             |
|---------------------------|-------------|
| Control/operation element | Push button |
| Number of poles           | 1           |

Materials

|                |            |
|----------------|------------|
| Colour         | Gold       |
| Surface finish | Glossy     |
| Material       | Brass      |
| Treatment      | Galvanised |
| Transparent    | No         |

Dimensions

|                                    |          |
|------------------------------------|----------|
| Height                             | 22 mm    |
| Width                              | 22 mm    |
| Depth                              | 19.70 mm |
| Built-in depth                     | 13 mm    |
| Built-in depth flush-mounted boxes | 0 mm     |

Controls and indicators

|                              |    |
|------------------------------|----|
| Number of buttons            | 1  |
| With feedback signal contact | No |

Safety

|                               |      |
|-------------------------------|------|
| Ingress Protection (IP) class | IP20 |
| Impact resistance IK          | IK07 |

Accessories

|                     |    |
|---------------------|----|
| Has labelling field | No |
|---------------------|----|

Use conditions

|                       |             |
|-----------------------|-------------|
| Operating temperature | -20 - 60 °C |
|-----------------------|-------------|

Texts

|                    |                        |
|--------------------|------------------------|
| Imprint            | Without imprint        |
| Installation mode  | For screw fastening    |
| Switch mode        | Normally open contact  |
| Type of connection | With plug-in terminals |

Sustainability

|                 |     |
|-----------------|-----|
| REACH-SVHC free | Yes |
| RoHS conform    | Yes |