



181112



Push-button, NO contact, TS, gold glossy, 24-carat galvanised

Technical Features

Electric current

Momentary contact current 1.50 A

Voltage

Rated voltage 12 V

Architecture

Control/operation element Push button

Number of poles 1

Materials

Colour Gold

Surface finish Glossy

Material Brass

Treatment Galvanised

Transparent No

Dimensions

Height 22 mm

Width 22 mm

Depth 19.70 mm

Built-in depth 13 mm

Built-in depth flush-mounted boxes 0 mm

Controls and indicators

Number of buttons 1

With feedback signal contact No

Safety

Ingress Protection (IP) class IP20

Impact resistance IK IK07

Accessories

Has labelling field No

Use conditions

Operating temperature -20 - 60 °C

Texts

Imprint Without imprint

Installation mode For screw fastening

Switch mode Normally open contact

Type of connection With plug-in terminals

Suitable for

TS

Sustainability

REACH-SVHC free Yes

RoHS conform Yes