



181113



**Push-button, NO contact, TS, stainless steel matt, brushed nickel**

**Technical Features**

**Electric current**

Momentary contact current 1.50 A

**Voltage**

Rated voltage 12 V

**Architecture**

Control/operation element Push button

Number of poles 1

**Materials**

Colour Stainless steel

Surface finish Matt

Material Brass  
Nickel  
Stainless steel

Treatment Brushed

Transparent No

**Dimensions**

Height 22 mm

Width 22 mm

Depth 19.70 mm

Built-in depth 13 mm

Built-in depth flush-mounted boxes 0 mm

**Controls and indicators**

Number of buttons 1

With feedback signal contact No

**Safety**

Ingress Protection (IP) class IP20

Impact resistance IK IK07

**Accessories**

Has labelling field No

**Use conditions**

Operating temperature -20 - 60 °C

**Texts**

Imprint Without imprint

Installation mode For screw fastening

Switch mode Normally open contact

Type of connection With plug-in terminals

**Sustainability**

REACH-SVHC free Yes

RoHS conform Yes