



181113



Push-button, NO contact, TS, stainless steel matt, brushed nickel

#### Technical Features

##### Electric current

Momentary contact current 1.50 A

##### Voltage

Rated voltage 12 V

##### Architecture

Control/operation element Push button

Number of poles 1

##### Materials

Colour Stainless steel

Surface finish Matt

Material Brass  
Nickel  
Stainless steel

Treatment Brushed

Transparent No

##### Dimensions

Height 22 mm

Width 22 mm

Depth 19.70 mm

Built-in depth 13 mm

Built-in depth flush-mounted boxes 0 mm

##### Controls and indicators

Number of buttons 1

With feedback signal contact No

##### Safety

Ingress Protection (IP) class IP20

Impact resistance IK IK07

##### Accessories

Has labelling field No

##### Use conditions

Operating temperature -20 - 60 °C

##### Texts

Imprint Without imprint

Installation mode For screw fastening

Switch mode Normally open contact

Type of connection With plug-in terminals

##### Suitable for

TS

##### Sustainability

REACH-SVHC free Yes

RoHS conform Yes