




EE804A



**Movement detector 360° surface mounted with normally open contact**

**Technical Features**

**Detection**

Detection angle	360 - 360
Type of sensor	Movement detector Presence detector

**Settings**

Time delay	5 S - 30 Min
------------	--------------

**Lighting**

Response brightness adjustable	5 - 1000 lx
--------------------------------	-------------

**Frequency**

Frequency	50 - 60 Hz
-----------	------------

**Dimensions**

Width	105.50 mm
Built-in depth	0 mm
Recommended installation height	2.5 - 3.5 m

**Use conditions**

Operating temperature	-5 - 45 °C
-----------------------	------------

**Materials**

Colour	White
Material	Plastic

**Safety**

Ingress Protection (IP) class	IP21
-------------------------------	------

**Installation, mounting**

Mounting on	Surface mounting
Suitable for outdoor usage	No

**Texts**

Function	Can only be used as individual unit
Installation mode	Installation possible on flush-mounted box For ceiling mounting
Type of connection	With screw terminals

**Sustainability**

REACH-SVHC free	Yes
RoHS conform	Yes