



85655273



KNX radio wall-transmitter 1gang flat quicklink, K.5, stainl. steel matt, lacq.

Technical Features

Settings

Supported configuration mode quicklink

Voltage

Operating voltage 3 - 3 V

Equipment

Number of channels 2

Transmitter duty cycle 1 %

Connectivity

Radio protocol KNX Radio

Receiver category 2

Use conditions

Operating temperature -5 - 45 °C

Dimensions

Assembling height 14 mm

Materials

Colour Stainless steel

Material Stainless steel
Thermoplastic

Safety

Ingress Protection (IP) class IP20

Texts

Function Easy additional functions: +6 scenes, on/off operating mode, 1 up/down button control
Reset function (to factory setting)

Protection With dismantling protection

Installation mode For flat surface mounting and extension of combinations

Sustainability

RoHS conform Yes