



KNX radio wall-transmitter 1gang flat quicklink, K.5, stainl. steel matt, lacq.

Technical Features

|                               |                                                                                                                              |
|-------------------------------|------------------------------------------------------------------------------------------------------------------------------|
| <b>Settings</b>               |                                                                                                                              |
| Supported configuration mode  | quicklink                                                                                                                    |
| <b>Voltage</b>                |                                                                                                                              |
| Operating voltage             | 3 - 3 V                                                                                                                      |
| <b>Equipment</b>              |                                                                                                                              |
| Number of channels            | 2                                                                                                                            |
| Transmitter duty cycle        | 1 %                                                                                                                          |
| <b>Connectivity</b>           |                                                                                                                              |
| Radio protocol                | KNX Radio                                                                                                                    |
| Receiver category             | 2                                                                                                                            |
| <b>Use conditions</b>         |                                                                                                                              |
| Operating temperature         | -5 - 45 °C                                                                                                                   |
| <b>Dimensions</b>             |                                                                                                                              |
| Assembling height             | 14 mm                                                                                                                        |
| <b>Materials</b>              |                                                                                                                              |
| Colour                        | Stainless steel                                                                                                              |
| Material                      | Stainless steel<br>Thermoplastic                                                                                             |
| <b>Safety</b>                 |                                                                                                                              |
| Ingress Protection (IP) class | IP20                                                                                                                         |
| <b>Texts</b>                  |                                                                                                                              |
| Function                      | Easy additional functions: +6 scenes, on/off operating mode, 1 up/down button control<br>Reset function (to factory setting) |
| Protection                    | With dismantling protection                                                                                                  |
| Installation mode             | For flat surface mounting and extension of combinations                                                                      |
| <b>Sustainability</b>         |                                                                                                                              |
| RoHS conform                  | Yes                                                                                                                          |