



75643130



**KNX glass sensor 3g thermostat, display, intg bus coupl. ,KNX-TS sensor, p.wh.**

### Technical Features

#### Installation, mounting

Mounting on Flush mounting

#### Use conditions

Operating temperature -5 - 45 °C

#### Functions

With room temperature controller Yes

#### Power

Current consumption 23 mA

#### Dimensions

Built-in depth 24.20 mm

Built-in depth flush-mounted boxes 27 mm

Height 160 mm

Width 86 mm

Depth 37.70 mm

#### Equipment

Number of actuation points 8

#### Controls and indicators

With LED indication Yes

#### Materials

Colour Polar white

RAL code 9010

Material Glass

Surface finish Glossy

#### Accessories

Has labelling field No

#### Screen

With display Yes

#### Texts

Function For switch, push-button, dimmer, blind and thermostat functions  
With valve protection function

Installation mode For vertical mounting

Operating mode Controller operating modes: comfort, standby, night and frost/heat protection mode

Temperature Additional connection for external temperature sensor  
Temperature measurement via internal Temperature sensor or external communication object

Voltage Operation with non-choked output of KNX voltage supply possible (pay attention to current consumption)  
Separate auxiliary power supply needed

#### Sustainability

REACH-SVHC free Yes

RoHS conform Yes