



**Technical Features**

**Installation, mounting**

Mounting on Flush mounting

**Use conditions**

Operating temperature -5 - 45 °C

**Functions**

With room temperature controller Yes

**Power**

Current consumption 23 mA

**Dimensions**

Built-in depth flush-mounted boxes 27 mm

Height 160 mm

Width 86 mm

Depth 5.70 mm

**Equipment**

Number of actuation points 6

**Controls and indicators**

With LED indication Yes

**Materials**

Colour Polar white

RAL code 9010

Material Glass

Surface finish Glossy

**Accessories**

Has labelling field No

**Screen**

With display Yes

**Texts**

Function For switch, push-button, dimmer, blind and thermostat functions  
With valve protection function

Installation mode For vertical mounting

Operating mode Controller operating modes: comfort, standby, night and frost/heat protection mode

Temperature Additional connection for external temperature sensor  
Temperature measurement via internal Temperature sensor or external communication object

Voltage Operation with non-choked output of KNX voltage supply possible (pay attention to current consumption)  
Separate auxiliary power supply needed