



HR440

EARTH LEAKAGE RELAY 0.03-3A TIME DELAY TORROID 25MM

Technical Features

Electric current	
Rated residual operating current I _{Δn}	30 mA 100 mA 300 mA 500 mA 1000 mA 3000 mA
Toroid's: Allowed overload	30 kA/100 ms

Safety	
Residual current type	A

Equipment	
With earth leakage toroid	No

Settings	
Adjustable time delay	Yes

Dimensions	
Maximum connection distance between receiver and transmitter	25 m und 50 m twisted pair

Sustainability	
REACH-SVHC free	Yes
RoHS conform	Yes