



KB190B

Insulated busbar 1P 100A prong 20mm² 57M

Technical Features

Electric current

| | |
|---------------|-------|
| Rated current | 100 A |
|---------------|-------|

Architecture

| | |
|-----------------|---|
| Number of poles | 1 |
|-----------------|---|

Dimensions

| | |
|--------|---------|
| Length | 1000 mm |
|--------|---------|

Voltage

| | |
|--------------------------------------|--------|
| Rated impulse withstand voltage Uimp | 4000 V |
|--------------------------------------|--------|

| | |
|------------------------------|-------------|
| Rated operational voltage Ue | 415 - 415 V |
|------------------------------|-------------|

Connection

| | |
|-------------------------------|--------------------|
| Cross-section rigid conductor | 20 mm ² |
|-------------------------------|--------------------|

| | |
|---------------------|-----------------------|
| Connector/plug type | Phase busbar with pin |
|---------------------|-----------------------|

Capacity

| | |
|-------------------|----|
| Number of modules | 57 |
|-------------------|----|

Sustainability

| | |
|--------------|-----|
| Halogen free | Yes |
|--------------|-----|

| | |
|--------------|-----|
| RoHS conform | Yes |
|--------------|-----|