



WGCHUSB35

### USB+3.5mm audio socket

#### Technical Features

##### Connection

Connector/plug type	USB
---------------------	-----

##### Frequency

Audio frequency	20 - 20000 Hz
-----------------	---------------

##### Materials

Colour	White
Surface finish	Glossy
Material	Polycarbonate (PC)

##### Dimensions

Height	86 mm
Width	86 mm
Depth	40 mm

##### Connectivity

Mounting type	Screw mounting
---------------	----------------

##### Equipment

With dust cover	No
-----------------	----

##### Safety

Ingress Protection (IP) class	IP20
-------------------------------	------

##### Texts

Labelling	Without labelling field
Supporting plate/supporting ring	With supporting ring

##### Suitable for

shark	
-------	--

##### Sustainability

RoHS conform	Yes
--------------	-----