



75643055



**Touch sensor 3gang thermostat, display, intg bus coupl. unit,KNX-R.3, glass bl.**

### Technical Features

#### Installation, mounting

Mounting on Flush mounting

#### Use conditions

Operating temperature -5 - 45 °C

#### Functions

With room temperature controller Yes

#### Power

Current consumption 23 mA

#### Dimensions

Built-in depth	12.90 mm
Built-in depth flush-mounted boxes	16 mm
Height	152 mm
Width	81 mm
Depth	23 mm

#### Equipment

Number of actuation points 8

#### Controls and indicators

With LED indication Yes

#### Materials

Colour	Black
RAL code	9005
Material	Glass
Surface finish	Glossy

#### Accessories

Has labelling field No

#### Screen

With display Yes

#### Texts

Function	For switch, push-button, dimmer, blind and thermostat functions With valve protection function
Installation mode	For vertical mounting
Operating mode	Controller operating modes: comfort, standby, night and frost/heat protection mode
Temperature	Additional connection for external temperature sensor Temperature measurement via internal Temperature sensor or external communication object
Voltage	Operation with non-choked output of KNX voltage supply possible (pay attention to current consumption) Separate auxiliary power supply needed

#### Sustainability

REACH-SVHC free	Yes
RoHS conform	Yes