



TJA560



IoT Controller

Technical Features

Equipment

Web server	Yes
------------	-----

Voltage

Operating voltage	24 - 24 V
Operating voltage over bus	21 - 32 V

Settings

Supported configuration mode	ETS easy
------------------------------	-------------

Safety

Ingress Protection (IP) class	IP20
-------------------------------	------

Use conditions

Operating temperature	0 - 45 °C
-----------------------	-----------

Controls and indicators

With LED indication	Yes
---------------------	-----

Dimensions

Number of width units	6
-----------------------	---

Texts

Labelling	Large labelling field
Installation mode	For installation in distribution box
Connectors jacks	With 2 USB jacks type B, USB 2.0 compliant
Type of connection	With quickconnect plug-in terminals