



29527009



LED signal light, red/green lighting, K.1, p. white glossy

Technical Features

Voltage

Rated voltage 230 V

Power

Power absorbed 0.50 W

Frequency

Frequency 50 - 60 Hz

Lighting

Type of lamp LED

Materials

Colour Polar white

RAL code 9010

Surface finish Glossy

Material Metal
Plastic

Treatment Untreated

Dimensions

Height 70 mm

Width 70 mm

Depth 50 mm

Connection

Conductor cross-section 2.50 - 2.50 mm²

Safety

Ingress Protection (IP) class IP20

Texts

Labelling Foil bi-colour with imprinted symbols for Do not disturb / Make up room and Enter/ Wait are supplied

Imprint Without imprint

Suitable for

K.x

Sustainability

REACH-SVHC free Yes

RoHS conform Yes