



29527004



LED signal light, red/green lighting, K.5, stainless steel matt, lacq.

Technical Features

Voltage

Rated voltage 230 V

Power

Power absorbed 0.50 W

Frequency

Frequency 50 - 60 Hz

Lighting

Type of lamp LED

Materials

Colour Stainless steel

RAL code 9022

Surface finish Matt

Material Metal
Plastic
Stainless steel

Treatment Varnished

Dimensions

Height 70 mm

Width 70 mm

Depth 50 mm

Connection

Conductor cross-section 2.50 - 2.50 mm²

Safety

Ingress Protection (IP) class IP20

Texts

Labelling Foil bi-colour with imprinted symbols for Do not disturb / Make up room and Enter/ Wait are supplied

Imprint Without imprint

Suitable for

K.x

Sustainability

REACH-SVHC free Yes

RoHS conform Yes