



HR502

Earth Leakage Relay 0.3A instantaneous Trip Type A

Technical Features

Electric current

Rated residual operating current I _{Δn}	300 mA
Toroid's: Allowed overload	30 kA/100 ms

Safety

Residual current type	A HI
-----------------------	------

Equipment

With earth leakage toroid	Yes
---------------------------	-----

Settings

Time delay of residual current	0 s
Adjustable time delay	No

Dimensions

Maximum connection distance between receiver and transmitter	25 m und 50 m twisted pair
--	----------------------------

Sustainability

REACH-SVHC free	Yes
RoHS conform	Yes