



HR510

Earth Leakage Relay 0.03-10A configurable Trip Type A

Technical Features

Electric current

Rated residual operating current I _{dn}	30 mA 100 mA 300 mA 500 mA 1000 mA 3000 mA 10000 mA
--	---

Toroid's: Allowed overload	30 kA/100 ms
----------------------------	--------------

Safety

Residual current type	A HI
-----------------------	------

Equipment

With earth leakage toroid	Yes
---------------------------	-----

Settings

Time delay of residual current	0 s
Adjustable time delay	Yes

Dimensions

Maximum connection distance between receiver and transmitter	25 m und 50 m twisted pair
--	----------------------------

Sustainability

Halogen free	Yes
REACH-SVHC free	Yes
RoHS conform	Yes