



HR510

**Earth Leakage Relay 0.03-10A configurable Trip Type A**

**Technical Features**

**Electric current**

Rated residual operating current I <sub>dn</sub>	30 mA 100 mA 300 mA 500 mA 1000 mA 3000 mA 10000 mA
--	---

Toroid's: Allowed overload	30 kA/100 ms
----------------------------	--------------

**Safety**

Residual current type	A HI
-----------------------	------

**Equipment**

With earth leakage toroid	Yes
---------------------------	-----

**Settings**

Time delay of residual current	0 s
Adjustable time delay	Yes

**Dimensions**

Maximum connection distance between receiver and transmitter	25 m und 50 m twisted pair
--	----------------------------

**Sustainability**

Halogen free	Yes
REACH-SVHC free	Yes
RoHS conform	Yes