



HR523

EARTH LEAKAGE RELAY 0.5-30A TIME DELAY 50% LED

Technical Features

Electric current

| | |
|--|----------|
| Rated residual operating current I _{Δn} | 500 mA |
| | 1000 mA |
| | 3000 mA |
| | 5000 mA |
| | 10000 mA |
| | 20000 mA |
| | 30000 mA |

| | |
|----------------------------|--------------|
| Toroid's: Allowed overload | 30 kA/100 ms |
|----------------------------|--------------|

Safety

| | |
|-----------------------|---|
| Residual current type | A |
|-----------------------|---|

Equipment

| | |
|---------------------------|-----|
| With earth leakage toroid | Yes |
|---------------------------|-----|

Settings

| | |
|-----------------------|-----|
| Adjustable time delay | Yes |
|-----------------------|-----|

Dimensions

| | |
|--|----------------------------|
| Maximum connection distance between receiver and transmitter | 25 m und 50 m twisted pair |
|--|----------------------------|

Sustainability

| | |
|-----------------|-----|
| Halogen free | Yes |
| REACH-SVHC free | Yes |
| RoHS conform | Yes |