



20448982



Thermostat, NO contact, centre plate, time-controlled, S.1, white glossy

Technical Features

Installation, mounting

Mounting on Flush mounting

Settings

Comfort temperature setpoint 10 - 40 °C

Dimensions

Height 71 mm

Width 71 mm

Depth 42 mm

Power supply

Supply voltage 230 V AC

Voltage

Nominal voltage 230 - 230 V

Electric current

Max. switching current 10 A

Materials

Colour White

Power

Standby power consumption (solstandby) 1.20 W

Use conditions

Energy efficiency class IV (2%)

Equipment

Switching temperature difference 0.50 K

Type of probe Sensor with resistor

Type of display LCD

Summer-/wintertime switchover Yes

Screen

With ambient temperature display Yes

Sustainability

REACH-SVHC free Yes

RoHS conform Yes