




85655131



KNX radio wall-transmitter 1gang flat solar quicklink, R.1/R.3, black glossy

Technical Features

Settings

Supported configuration mode	quicklink
------------------------------	-----------

Voltage

Operating voltage	3 - 3 V
-------------------	---------

Equipment

Number of channels	2
Transmitter duty cycle	1 %

Connectivity

Radio protocol	KNX Radio
Receiver category	2

Use conditions

Operating temperature	-5 - 45 °C
-----------------------	------------

Dimensions

Assembling height	14 mm
-------------------	-------

Materials

Colour	Black
Material	Thermoplastic

Safety

Ingress Protection (IP) class	IP20
-------------------------------	------

Texts

Function	Easy additional functions: +6 scenes, on/off operating mode, 1 up/down button control Reset function (to factory setting)
Protection	With dismantling protection
Voltage	Power supply via solar cells
Installation mode	For flat surface mounting and extension of combinations

Sustainability

Halogen free	Yes
REACH-SVHC free	Yes
RoHS conform	Yes