



85655189



**KNX radio wall-transmitter 1gang flat solar quicklink, S.1/B.3/B.7, p.white gl.**

**Technical Features**

**Settings**

Supported configuration mode	quicklink
------------------------------	-----------

**Voltage**

Operating voltage	3 - 3 V
-------------------	---------

**Equipment**

Number of channels	2
Transmitter duty cycle	1 %

**Connectivity**

Radio protocol	KNX Radio
Receiver category	2

**Use conditions**

Operating temperature	-5 - 45 °C
-----------------------	------------

**Dimensions**

Assembling height	14 mm
-------------------	-------

**Materials**

Colour	Polar white
Material	Thermoplastic

**Safety**

Ingress Protection (IP) class	IP20
-------------------------------	------

**Texts**

Function	Easy additional functions: +6 scenes, on/off operating mode, 1 up/down button control Reset function (to factory setting)
Protection	With dismantling protection
Voltage	Power supply via solar cells
Installation mode	For flat surface mounting and extension of combinations

**Sustainability**

Halogen free	Yes
REACH-SVHC free	Yes
RoHS conform	Yes