



VS412TTQ

Small distributor,golf,surface,4row,IP40,48M,QC-terminal,N+PE,transparent door

### Technical Features

#### Installation, mounting

Mounting on	Surface mounting
-------------	------------------

#### Electric current

Rated current	63 A
---------------	------

#### Equipment

Number of rails	2
Number of rows	4
With lock	No
Has neutral terminal block	Yes

#### Capacity

Number of modules	24
-------------------	----

#### Dimensions

Height	647 mm
Width	282 mm
Depth	99 mm

#### Cover, door

Number of cabinet doors	1
Number of locks	0

#### Dimensions

Number of width units	12
-----------------------	----

#### Cover, door

Door/cover is transparent	Yes
---------------------------	-----

#### Materials

Material	Plastic
RAL code	9010
Colour	Pure white

#### Equipment

Has earthing terminal block	Yes
Has mounting plate	No

#### Safety

Protection class	Isolation class II
Impact resistance IK	IK07
Ingress Protection (IP) class	IP40
Locking type	Snap on lock Without lock
Glow wire test	650 °C

#### Sustainability

RoHS conform	Yes
--------------	-----