



50463525



Push-button insert, change-over contact, illuminated surf.-/flush-mtd, W.1, grey m.

**Technical Features**

**Electric current**

Momentary contact current 10 A

**Voltage**

Rated voltage 250 V

**Architecture**

Control/operation element Rocker

**Materials**

Colour Grey

Surface finish Matt

Material Thermoplastic

Treatment Untreated

Transparent No

**Dimensions**

Height 55 mm

Width 55 mm

Depth 41 mm

Built-in depth flush-mounted boxes 0 mm

**Installation, mounting**

Mounting on Flush mounting  
Surface mounting

**Controls and indicators**

Number of buttons 1

Type of push button Single push button

With feedback signal contact No

**Safety**

Ingress Protection (IP) class IP55

Impact resistance IK IK05

**Accessories**

Has labelling field No

**Use conditions**

Operating temperature -25 - 35 °C

**Texts**

Imprint Without imprint

Installation mode For screw fastening

Lighting With blue 230 V LED unit  
For lighting and monitoring circuit

Type of connection With N-terminal  
With plug-in terminals