



50463525

Push-button insert, change-over contact, illuminated surf.-/flush-mtd, W.1, grey m.

Technical Features

Electric current

Momentary contact current	10 A
---------------------------	------

Voltage

Rated voltage	250 V
---------------	-------

Architecture

Control/operation element	Rocker
---------------------------	--------

Materials

Colour	Grey
Surface finish	Matt
Material	Thermoplastic
Treatment	Untreated
Transparent	No

Dimensions

Height	55 mm
Width	55 mm
Depth	41 mm
Built-in depth flush-mounted boxes	0 mm

Installation, mounting

Mounting on	Flush mounting Surface mounting
-------------	------------------------------------

Controls and indicators

Number of buttons	1
Type of push button	Single push button
With feedback signal contact	No

Safety

Ingress Protection (IP) class	IP55
Impact resistance IK	IK05

Use conditions

Operating temperature	-25 - 35 °C
-----------------------	-------------

Texts

Imprint	Without imprint
Installation mode	For screw fastening
Lighting	With blue 230 V LED unit For lighting and monitoring circuit
Type of connection	With N-terminal With plug-in terminals