



HR402

EARTH LEAKAGE RELAY 0.3A INSTANT TRIP

Technical Features

Frequency

| | |
|-----------|------------|
| Frequency | 50 - 60 Hz |
|-----------|------------|

Voltage

| | |
|--------------------------------------|--------|
| Rated impulse withstand voltage Uimp | 4000 V |
|--------------------------------------|--------|

Power

| | |
|---------------------------|-----|
| Total power loss under IN | 3 W |
|---------------------------|-----|

Safety

| | |
|-------------------------------|------|
| Ingress Protection (IP) class | IP30 |
|-------------------------------|------|

Use conditions

| | |
|-----------------------|-------------|
| Operating temperature | -10 - 55 °C |
|-----------------------|-------------|

Connection

| | |
|----------------------------------|-------------------------|
| Cross-section flexible conductor | 1.5 - 6 mm ² |
|----------------------------------|-------------------------|

| | |
|-------------------------------|--------------------------|
| Cross-section rigid conductor | 1.5 - 10 mm ² |
|-------------------------------|--------------------------|

Installation, mounting

| | |
|---------------------------|----------------|
| Nominal tightening torque | 1.70 - 1.70 Nm |
|---------------------------|----------------|

Sustainability

| | |
|-----------------|-----|
| REACH-SVHC free | Yes |
|-----------------|-----|

| | |
|--------------|-----|
| RoHS conform | Yes |
|--------------|-----|