



HR400

EARTH LEAKAGE RELAY 0.03A INSTANT TRIP

Technical Features

Frequency

Frequency 50 - 60 Hz

Voltage

Rated impulse withstand voltage U_{imp} 4000 V

Power

Total power loss under IN 3 W

Safety

Ingress Protection (IP) class IP30

Use conditions

Operating temperature -10 - 55 °C

Connection

Cross-section flexible conductor 1.5 - 6 mm²

Cross-section rigid conductor 1.5 - 10 mm²

Installation, mounting

Nominal tightening torque 1.70 - 1.70 Nm

Sustainability

REACH-SVHC free Yes

RoHS conform Yes