



HR400

### EARTH LEAKAGE RELAY 0.03A INSTANT TRIP

#### Technical Features

##### Frequency

Frequency	50 - 60 Hz
-----------	------------

##### Voltage

Rated impulse withstand voltage Uimp	4000 V
--------------------------------------	--------

##### Power

Total power loss under IN	3 W
---------------------------	-----

##### Safety

Ingress Protection (IP) class	IP30
-------------------------------	------

##### Use conditions

Operating temperature	-10 - 55 °C
-----------------------	-------------

##### Connection

Cross-section flexible conductor	1.5 - 6 mm <sup>2</sup>
----------------------------------	-------------------------

Cross-section rigid conductor	1.5 - 10 mm <sup>2</sup>
-------------------------------	--------------------------

##### Installation, mounting

Nominal tightening torque	1.70 - 1.70 Nm
---------------------------	----------------

##### Sustainability

REACH-SVHC free	Yes
-----------------	-----

RoHS conform	Yes
--------------	-----