



HA305

Load break switch with visible breaking 3P 250A with short handel

Technical Features

Electric current

Rated current	250 A
Acceptable current rating AC21 category A	250 A
Acceptable current rating AC21 category B	250 A
Acceptable current rating AC22 category A	250 A
Acceptable current rating AC22 category B	250 A
Acceptable current rating AC23 category A	250 A
Acceptable current rating AC23 category B	250 A

Architecture

Type of pole	3P
Number of poles	3

Connection

Cross-section rigid conductor	95 mm ²
Cross-section flexible conductor	95 mm ²

Voltage

Rated insulation voltage U_i	800 V
Rated impulse withstand voltage U_{imp}	8000 V
Rated operational voltage U_e	380 - 415 V

Power

Power loss per pole at I_n	9.10 W
Total power loss under I_N	27.30 W

Equipment

Number of auxiliary contacts as change-over contact	0
Number of auxiliary contacts as normally closed contact	0
Number of auxiliary contacts as normally open contact	0

Use conditions

Operating temperature	-20 - 70 °C
-----------------------	-------------

Capacity

Number of modules	8.50
-------------------	------

Dimensions

Height	150 mm
Width	142 mm
Depth	90 mm

Sustainability

REACH-SVHC free	Yes
RoHS conform	Yes