



FWB52M2

FWB encl. univers,IP44,class II, 5x26mod.,800x550x161mm,QuickConnect

### Technical Features

#### Installation, mounting

|                            |                  |
|----------------------------|------------------|
| Suitable for outdoor usage | No               |
| Mounting on                | Surface mounting |

#### Electric current

|               |       |
|---------------|-------|
| Rated current | 125 A |
|---------------|-------|

#### Equipment

|                            |    |
|----------------------------|----|
| Number of rails            | 5  |
| Number of rows             | 5  |
| Number of section in width | 2  |
| With lock                  | No |
| Has neutral terminal block | No |

#### Capacity

|                   |     |
|-------------------|-----|
| Number of modules | 130 |
|-------------------|-----|

#### Functions

|                     |     |
|---------------------|-----|
| With conduit inlets | Yes |
|---------------------|-----|

#### Dimensions

|        |        |
|--------|--------|
| Height | 800 mm |
| Width  | 550 mm |
| Depth  | 165 mm |

#### Cover, door

|                         |   |
|-------------------------|---|
| Number of cabinet doors | 1 |
| Number of locks         | 0 |

#### Dimensions

|                       |    |
|-----------------------|----|
| Number of width units | 26 |
|-----------------------|----|

#### Cover, door

|                           |                       |
|---------------------------|-----------------------|
| Type of handle            | Hinged pattern handle |
| Door/cover is transparent | No                    |

#### Connection

|                          |   |
|--------------------------|---|
| Number of conduit inlets | 8 |
|--------------------------|---|

#### Materials

|          |            |
|----------|------------|
| Material | Steel      |
| RAL code | 9010       |
| Colour   | Pure white |

#### Equipment

|                             |    |
|-----------------------------|----|
| Has earthing terminal block | No |
| Has mounting plate          | No |

#### Safety

|                               |                    |
|-------------------------------|--------------------|
| Protection class              | Isolation class II |
| Impact resistance IK          | IK09               |
| Ingress Protection (IP) class | IP44               |
| Locking type                  | Bar lock           |

#### Sustainability

|              |     |
|--------------|-----|
| RoHS conform | Yes |
|--------------|-----|