



1096608900

**Centre plate rotary knob 3-step switch neutral position, Q.x pol wh velv**

**Technical Features**

**Architecture**

Control/operation element	Rotative
---------------------------	----------

**Materials**

Colour	Polar white
RAL code	9010
Surface finish	Velvety
Material	Duroplastic
Treatment	Untreated

**Dimensions**

Height	58.80 mm
Width	58.80 mm
Depth	30.50 mm

**Connectivity**

Mounting type	Screw mounting
---------------	----------------

**Equipment**

Monitoring window/light outlet	No
--------------------------------	----

**Accessories**

Has labelling field	No
---------------------	----

**Safety**

Ingress Protection (IP) class	IP20
Usable in higher IP class	IP44 in combination with sealing set

**Texts**

Imprint	With imprint
Installation mode	For screw fastening

**Identification**

Assembly arrangement	Central cover plate
----------------------	---------------------

**Suitable for**

Q.x	
-----	--

**Sustainability**

Halogen free	Yes
REACH-SVHC free	Yes
RoHS conform	Yes