



HR534

EARTH LEAKAGE RELAY 0.03-30A TIME DELAY 50% LCD TEST 4 WAYS

Technical Features

Electric current

Rated residual operating current I <sub>dn</sub>	30 mA
	100 mA
	300 mA
	500 mA
	1000 mA
	3000 mA
	5000 mA
	10000 mA

Toroid's: Allowed overload	30 kA/100 ms
----------------------------	--------------

Safety

Residual current type	A
-----------------------	---

Equipment

With earth leakage toroid	Yes
---------------------------	-----

Settings

Adjustable time delay	Yes
-----------------------	-----

Dimensions

Maximum connection distance between receiver and transmitter	25 m und 50 m twisted pair
--	----------------------------

Sustainability

REACH-SVHC free	Yes
RoHS conform	Yes