



WGDL121NPKB

**10A 2G press switch with led;kb**

**Technical Features**

**Electric current**

|                   |      |
|-------------------|------|
| Switching current | 10 A |
|-------------------|------|

**Voltage**

|               |       |
|---------------|-------|
| Rated voltage | 250 V |
|---------------|-------|

**Architecture**

|                           |               |
|---------------------------|---------------|
| Control/operation element | Double rocker |
|---------------------------|---------------|

**Materials**

|                |                    |
|----------------|--------------------|
| Colour         | Knight black       |
| Surface finish | Matt               |
| Material       | Polycarbonate (PC) |
| Treatment      | Varnished          |
| Transparent    | No                 |

**Dimensions**

|                                    |       |
|------------------------------------|-------|
| Height                             | 86 mm |
| Width                              | 86 mm |
| Depth                              | 25 mm |
| Built-in depth flush-mounted boxes | 35 mm |

**Controls and indicators**

|                   |   |
|-------------------|---|
| Number of buttons | 2 |
|-------------------|---|

**Connectivity**

|                    |                |
|--------------------|----------------|
| Type of connection | Screw terminal |
|--------------------|----------------|

**Safety**

|                               |      |
|-------------------------------|------|
| Ingress Protection (IP) class | IP20 |
|-------------------------------|------|

**Texts**

|             |       |
|-------------|-------|
| Switch mode | 1-way |
|-------------|-------|

**Suitable for**

|             |  |
|-------------|--|
| Hager shark |  |
|-------------|--|

**Sustainability**

|                 |     |
|-----------------|-----|
| REACH-SVHC free | Yes |
| RoHS conform    | Yes |