



BRA652101DELN

**Wall trunking base f-mounted BRA 68x210mm lid 2x80mm of alu natural anodized**

**Technical Features**

**Dimensions**

Height	68 mm
Width	210 mm
Length	2000 mm

**Cover, door**

Number of mountable lids	2
Cover width 1	80 mm
Cover width 2	80 mm
Cover width 3	0 mm

**Dimensions**

Inner cross-section	12060 - 12060 mm <sup>2</sup>
---------------------	-------------------------------

**Capacity**

Max. number of cables (Ø11 mm, 50% filled, with devices)	23
Max. number of cables (Ø11mm, 50% filled, without devices)	50

**Compatibility**

Device installation compatible format	Standard 60 mm, CEE, Ecoline, EIB, MCBs
---------------------------------------	---

**Installation, mounting**

Base perforation	Yes
------------------	-----

**Materials**

Material	Aluminium
Treatment	Anodised
Colour	Aluminium

**Safety**

Impact resistance IK	IK07
Ingress Protection (IP) class	IP40

**Use conditions**

Operating temperature	-5 - 90 °C
-----------------------	------------

**Connectivity**

Trunking coupling	Couplers as separate reference
-------------------	--------------------------------

**Equipment**

Cable retaining clip included	No
Number of cable retainers per meter	0
With protective film	Yes

**Sustainability**

REACH-SVHC free	Yes
RoHS conform	Yes

Illustrations | Drawings

