



BRA652101DELN

Wall trunking base f-mounted BRA 68x210mm lid 2x80mm of alu natural anodized

Technical Features

Dimensions

Height	68 mm
Width	210 mm
Length	2000 mm

Cover, door

Number of mountable lids	2
Cover width 1	80 mm
Cover width 2	80 mm
Cover width 3	0 mm

Dimensions

Inner cross-section	12060 - 12060 mm ²
---------------------	-------------------------------

Capacity

Max. number of cables (Ø11 mm, 50% filled, with devices)	23
Max. number of cables (Ø11mm, 50% filled, without devices)	50

Compatibility

Device installation compatible format	Standard 60 mm, CEE, Ecoline, EIB, MCBs
---------------------------------------	---

Installation, mounting

Base perforation	Yes
------------------	-----

Materials

Material	Aluminium
Treatment	Anodised
Colour	Aluminium

Safety

Impact resistance IK	IK07
Ingress Protection (IP) class	IP40

Use conditions

Operating temperature	-5 - 90 °C
-----------------------	------------

Connectivity

Trunking coupling	Couplers as separate reference
-------------------	--------------------------------

Equipment

Cable retaining clip included	No
Number of cable retainers per meter	0
With protective film	Yes

Sustainability

Halogen free	Yes
REACH-SVHC free	Yes
RoHS conform	Yes

Illustrations | Drawings

