



WGDL121NPEG

**10A 2G press switch with led;eg**

**Technical Features**

**Electric current**

Switching current	10 A
-------------------	------

**Voltage**

Rated voltage	250 V
---------------	-------

**Architecture**

Control/operation element	Double rocker
---------------------------	---------------

**Materials**

Colour	Gold
Surface finish	Matt
Material	Polycarbonate (PC)
Treatment	Varnished
Transparent	No

**Dimensions**

Height	86 mm
Width	86 mm
Depth	25 mm
Built-in depth flush-mounted boxes	35 mm

**Controls and indicators**

Number of buttons	2
With feedback signal contact	No

**Connectivity**

Type of connection	Screw terminal
--------------------	----------------

**Safety**

Ingress Protection (IP) class	IP20
-------------------------------	------

**Accessories**

Has labelling field	No
---------------------	----

**Texts**

Switch mode	1-way
-------------	-------

**Suitable for**

shark	
-------	--

**Sustainability**

RoHS conform	Yes
--------------	-----