



HIC425E

ATS with energy management 4x 125A

Technical Features

Voltage

Rated operational voltage Ue	380 - 415 V
------------------------------	-------------

Electric current

Rated current	125 A
---------------	-------

Rated conditional short-circuit current Icc with gl-gG fuses	100 kA
--	--------

Power

Rated operational power under 400 V AC AC1	82000 W
--	---------

Architecture

Number of poles	4
-----------------	---

Device construction type	Fixed built-in
--------------------------	----------------

Compatibility

Suitable for DIN Rail	Yes
-----------------------	-----

Suitable for distribution board	Yes
---------------------------------	-----