



HIC425E

**ATS with energy management 4x 125A**

**Technical Features**

**Voltage**

|                                          |             |
|------------------------------------------|-------------|
| Rated operational voltage U <sub>e</sub> | 380 - 415 V |
|------------------------------------------|-------------|

**Electric current**

|                                                                          |        |
|--------------------------------------------------------------------------|--------|
| Rated current                                                            | 125 A  |
| Rated conditional short-circuit current I <sub>cc</sub> with gl-gG fuses | 100 kA |

**Power**

|                                            |         |
|--------------------------------------------|---------|
| Rated operational power under 400 V AC AC1 | 82000 W |
|--------------------------------------------|---------|

**Architecture**

|                          |                |
|--------------------------|----------------|
| Number of poles          | 4              |
| Device construction type | Fixed built-in |

**Compatibility**

|                                 |     |
|---------------------------------|-----|
| Suitable for DIN Rail           | Yes |
| Suitable for distribution board | Yes |