



WXF616N

Key switch gallery 3 positions 2 modules night

Technical Features

Frequency

Frequency	50 - 60 Hz
-----------	------------

Materials

Colour	Jet black
RAL code	9005
Surface finish	Satin finish
Material	Metal Plastic
Treatment	Varnished

Identification

Assembly arrangement	Basic element with central cover plate
----------------------	--

Connectivity

Mounting type	Click mounting
---------------	----------------

Controls and indicators

Number of buttons	0
-------------------	---

Dimensions

Dimensions	45 x 45 mm
Built-in depth	34 mm
Built-in depth flush-mounted boxes	34 mm

Safety

Ingress Protection (IP) class	IP20
Impact resistance IK	IK02

Architecture

Control/operation element	Key
---------------------------	-----

Electric current

Rated current	1.20 A
---------------	--------

Texts

Lighting	Without lighting (cannot be illuminated)
Switch mode	With neutral position "OFF": OFF-1-2-3

Sustainability

Halogen free	Yes
REACH-SVHC free	Yes
RoHS conform	Yes