



WXF617N

### Key switch gallery 3 positions extraction in 0 night

#### Technical Features

##### Frequency

Frequency	50 - 60 Hz
-----------	------------

##### Materials

Colour	Jet black
RAL code	9005
Surface finish	Satin finish
Material	Polycarbonate (PC)
Treatment	Varnished

##### Identification

Assembly arrangement	Basic element with central cover plate
----------------------	--

##### Connectivity

Mounting type	Click mounting
---------------	----------------

##### Controls and indicators

Number of buttons	0
-------------------	---

##### Dimensions

Dimensions	40 x 45 mm
Built-in depth	34 mm
Built-in depth flush-mounted boxes	34 mm

##### Safety

Ingress Protection (IP) class	IP20
Impact resistance IK	IK02

##### Architecture

Control/operation element	Key
---------------------------	-----

##### Electric current

Rated current	16 A
---------------	------

##### Texts

Lighting	Without lighting (cannot be illuminated)
Switch mode	Group switch 1-0-2