



WXF615T

### Key switch gallery 2 positions 2 modules titane

#### Technical Features

##### Frequency

Frequency	50 - 60 Hz
-----------	------------

##### Materials

Colour	Titanium
RAL code	9006
Surface finish	Satin finish
Material	Metal Plastic
Treatment	Varnished

##### Identification

Assembly arrangement	Basic element with central cover plate
----------------------	--

##### Connectivity

Mounting type	Click mounting
---------------	----------------

##### Controls and indicators

Number of buttons	0
-------------------	---

##### Dimensions

Built-in depth	34 mm
Built-in depth flush-mounted boxes	34 mm

##### Safety

Ingress Protection (IP) class	IP20
Impact resistance IK	IK02

##### Architecture

Control/operation element	Key
---------------------------	-----

##### Electric current

Rated current	10 A
---------------	------

##### Texts

Lighting	Without lighting (cannot be illuminated)
Switch mode	2x 1- -pole off

##### Sustainability

REACH-SVHC free	Yes
RoHS conform	Yes