



WXF615T

Key switch gallery 2 positions 2 modules titane

Technical Features

Frequency

Frequency	50 - 60 Hz
-----------	------------

Materials

Colour	Titanium
RAL code	9006
Surface finish	Satin finish
Material	Metal Plastic
Treatment	Varnished

Identification

Assembly arrangement	Basic element with central cover plate
----------------------	--

Connectivity

Mounting type	Click mounting
---------------	----------------

Controls and indicators

Number of buttons	0
-------------------	---

Dimensions

Built-in depth	34 mm
Built-in depth flush-mounted boxes	34 mm

Safety

Ingress Protection (IP) class	IP20
Impact resistance IK	IK02

Architecture

Control/operation element	Key
---------------------------	-----

Electric current

Rated current	10 A
---------------	------

Texts

Lighting	Without lighting (cannot be illuminated)
Switch mode	2x 1- -pole off

Sustainability

REACH-SVHC free	Yes
RoHS conform	Yes