



450502



Loudspeaker soc. out. High End, com-tech

Technical Features

Connection

Connector/plug type	Loudspeaker socket
Conductor cross-section	10 - 10 mm ²

Materials

Material	Metal Plastic
Treatment	Untreated

Dimensions

Height	71 mm
Width	71 mm
Depth	41.90 mm
Built-in depth flush-mounted boxes	0 mm
Built-in depth	31 mm

Connectivity

Mounting type	Claw mounting
---------------	---------------

Equipment

Shielded	No
With dust cover	No

Safety

Ingress Protection (IP) class	IP20
Impact resistance IK	IK02

Texts

Outlet	With straight outlet
Labelling	Without labelling field
Supporting plate/supporting ring	With supporting ring

Suitable for

K.x / Q.x / R.x / S.x/B.x	
---------------------------	--

Sustainability

REACH-SVHC free	Yes
RoHS conform	Yes