



VML\_SIZE\_3

**6 Way 63A 30mA Type A RCCB Incomer**

**Technical Features**

**Installation, mounting**

Mounting on	Surface mounting
-------------	------------------

**Functions**

Has protection main switch	Yes
Overvoltage protection	Yes

**Capacity**

Number of modules	6
-------------------	---

**Electric current**

Rated current	63 A
---------------	------

**Dimensions**

Depth	98.20 mm
Height	245 mm
Width	225 mm

**Cover, door**

Interlockable	No
Door/cover is transparent	No

**Materials**

Colour	Pure white
Material	Steel

**Connection**

Number of accessible phases	1
-----------------------------	---

**Scope of delivery**

Number of earth leakage circuit breaker type A	1
Number of RCCB in enclosure	1

**Equipment**

With socket outlet	No
--------------------	----

**Safety**

Ingress Protection (IP) class	IP2XC
Number of earth leakage switches 300 mA	0

**Sustainability**

RoHS conform	Yes
--------------	-----