

**Moulded Case Circuit Breaker h3 x160 TM FIX 3P3D 35A 18kA FTC**

**Technical Features**

**Electric current**

Rated current	35 A
Rated ultimate short-circuit breaking capacity Icu under 400 V AC IEC 60947-2	18 kA
Rated ultimate short-circuit breaking capacity Icu under 240 V AC IEC 60947-2	25 kA
Rated service breaking capacity Ics under 230 V AC according to IEC 60947-2	25 kA
Rated service breaking capacity Ics under 400 V AC according to IEC 60947-2	18 kA

**Architecture**

Number of poles	3
Control/operation element	Toggle
Device construction type	Fixed built-in

**Tripping**

Response time when opening	10 ms
----------------------------	-------

**Frequency**

Frequency	50 - 60 Hz
-----------	------------

**Voltage**

Rated impulse withstand voltage Uimp	8000 V
Rated insulation voltage Ui	690 V

**Functions**

Trip unit	TM F/F
-----------	--------

**Endurance**

Electric endurance in number of cycles	10000
Number of mechanical operations	20000

**Safety**

Ingress Protection (IP) class	IP4X
-------------------------------	------

**Connection**

Cross-section flexible conductor	4 - 70 mm <sup>2</sup>
Cross-section rigid conductor	4 - 95 mm <sup>2</sup>

**Installation, mounting**

Nominal tightening torque	2 - 2 Nm
Mounting-/Connection Position	Front

**Settings**

Thermal protection knob setting xIN	1
Adjustment range short-term delayed short-circuit release	0 - 0 A

**Compatibility**

Suitable for DIN Rail	No
-----------------------	----

**Main electrical attributes**

Magnetic protection trip time	0 - 0 ms
-------------------------------	----------

**Sustainability**

REACH-SVHC free	Yes
RoHS conform	Yes