



75314021



**Technical Features**

**Voltage**

Operating voltage over bus	21 - 32 V
Auxiliary tension	230 - 230 V

**Frequency**

Frequency	50 - 60 Hz
-----------	------------

**Use conditions**

Operating temperature	-5 - 45 °C
-----------------------	------------

**Equipment**

Number of outputs	4
-------------------	---

**Capacity**

Number of modules	8
-------------------	---

**Power**

Power of variator	7 - 250 W
-------------------	-----------

**Connectivity**

With bus system KNX radio	No
---------------------------	----

**Settings**

Supported configuration mode	ETS
------------------------------	-----

**Texts**

Fuse	Short-circuit and overload-proof (electronic fuse)
Dimming principle	Operating with LED and energy-saving lamps according to appropriate ETS configuration Phase cut-on or cut-off according to load type, self-learning
Function	Operating hours meter as forward or backward counter per channel Stairway function with switch-off warning according to DIN 18015-2
Type of connection	With screw terminals

**Sustainability**

REACH-SVHC free	Yes
RoHS conform	Yes