



LNH1250M

HRC LV fuse NH1 gG AC500V250A double indicator with live gripping-lugs

Technical Features

Architecture

Curve	gG
-------	----

Fuse

Fuse size	NH1
-----------	-----

Fuse characteristics	gG
----------------------	----

Voltage

Type voltage supply	AC/DC
---------------------	-------

Electric current

Rated current	250 A
---------------	-------

Use conditions

Insulated	No
-----------	----

Main electrical attributes

Rated short-circuit breaking capacity Icn AC according to IEC 60898-1	120 kA
-----------------------------------------------------------------------	--------

Power

Total power loss under IN	20 W
---------------------------	------

Dimensions

Height	64.50 mm
--------	----------

Width	135 mm
-------	--------

Depth	135 mm
-------	--------

Sustainability

Halogen free	Yes
--------------	-----

REACH-SVHC free	Yes
-----------------	-----

RoHS conform	Yes
--------------	-----