



FWU61S

**FW flush encl. 6-rows 72 modules, IP30, classII, niche 957x315x115mm**

### Technical Features

#### Installation, mounting

Suitable for outdoor usage	No
Mounting on	Flush mounting Hollow wall

#### Electric current

Rated current	125 A
---------------	-------

#### Equipment

Number of rails	6
Number of rows	6
Number of section in width	1
With lock	No
Has neutral terminal block	Yes

#### Capacity

Number of modules	72
-------------------	----

#### Functions

Has protection main switch	No
With conduit inlets	Yes

#### Dimensions

Height	1003 mm
Width	353 mm
Depth	125 mm
Built-in height	952 mm
Built-in width	310 mm

#### Cover, door

Number of cabinet doors	1
-------------------------	---

#### Dimensions

Built-in depth	112 mm
Number of width units	12

#### Cover, door

Type of handle	Hinged pattern handle
Door/cover is transparent	No

#### Connection

Number of conduit inlets	2
--------------------------	---

#### Connectivity

Mounting type	Screw mounting
---------------	----------------

#### Materials

Material	Steel
RAL code	9010
Colour	Pure white

#### Equipment

Has earthing terminal block	Yes
Has mounting plate	No

#### Safety

Protection class	Isolation class II
Impact resistance IK	IK09
Ingress Protection (IP) class	IP30

<b>Safety</b>	
Locking type	Without lock
Glow wire test	850 °C
<b>Sustainability</b>	
RoHS conform	Yes