



FWU63S

**FW flush encl. 6-rows 216 modules, IP30, classII, niche 957x815x115mm**

### Technical Features

#### Installation, mounting

|                            |                               |
|----------------------------|-------------------------------|
| Suitable for outdoor usage | No                            |
| Mounting on                | Flush mounting<br>Hollow wall |

#### Electric current

|               |       |
|---------------|-------|
| Rated current | 125 A |
|---------------|-------|

#### Equipment

|                            |     |
|----------------------------|-----|
| Number of rails            | 18  |
| Number of rows             | 6   |
| Number of section in width | 3   |
| With lock                  | No  |
| Has neutral terminal block | Yes |

#### Capacity

|                   |     |
|-------------------|-----|
| Number of modules | 216 |
|-------------------|-----|

#### Functions

|                            |     |
|----------------------------|-----|
| Has protection main switch | No  |
| With conduit inlets        | Yes |

#### Dimensions

|                 |         |
|-----------------|---------|
| Height          | 1003 mm |
| Width           | 853 mm  |
| Depth           | 125 mm  |
| Built-in height | 952 mm  |
| Built-in width  | 810 mm  |

#### Cover, door

|                         |   |
|-------------------------|---|
| Number of cabinet doors | 2 |
|-------------------------|---|

#### Dimensions

|                       |        |
|-----------------------|--------|
| Built-in depth        | 112 mm |
| Number of width units | 36     |

#### Cover, door

|                           |                       |
|---------------------------|-----------------------|
| Type of handle            | Hinged pattern handle |
| Door/cover is transparent | No                    |

#### Connection

|                          |   |
|--------------------------|---|
| Number of conduit inlets | 6 |
|--------------------------|---|

#### Connectivity

|               |                |
|---------------|----------------|
| Mounting type | Screw mounting |
|---------------|----------------|

#### Materials

|          |            |
|----------|------------|
| Material | Steel      |
| RAL code | 9010       |
| Colour   | Pure white |

#### Equipment

|                             |     |
|-----------------------------|-----|
| Has earthing terminal block | Yes |
| Has mounting plate          | No  |

#### Safety

|                               |                    |
|-------------------------------|--------------------|
| Protection class              | Isolation class II |
| Impact resistance IK          | IK09               |
| Ingress Protection (IP) class | IP30               |

Safety

|                |              |
|----------------|--------------|
| Locking type   | Without lock |
| Glow wire test | 850 °C       |

Sustainability

|              |     |
|--------------|-----|
| RoHS conform | Yes |
|--------------|-----|